
1/21/0



APPLICATIONS

- ➤ Low-Cost Analog and Digital Data Links
- ➤ Digitized Audio
- ➤ Optical Sensors
- ➤ Medical Instruments
- ➤ Robotics Communications
- ➤ Motor Controller Triggering
- ➤ EMC/EMI Signal Isolation
- ➤ Electronic Games
- ➤ Intra-System Links: Board-to-Board, Rack-to-Rack

DESCRIPTION

The IF-E91A is a high-output medium-speed infrared LED in a "connector-less" style plastic fiber optic package. The output spectrum peaks at 950 nm for the IF-E91A. The device package features an internal micro-lens, and a precision-molded PBT housing ensures efficient optical coupling with standard 1000 μm plastic fiber cable.

APPLICATION HIGHLIGHTS

The high output and fast transition times of the IF-E91A is suitable for low-cost analog and digital data links. Used with an IF-D96 photologic detector, the IF-E91A can achieve data rates of 500 kbps at link distances up to 7 m. The drive circuit design is simpler than required for laser diodes, making the IF-E91A an excellent low-cost alternative in a variety of analog and digital applications.

FEATURES

- ◆ Excellent Linearity
- ◆ No Optical Design Required
- ♦ Mates with Standard 1000 µm Core Jacketed Plastic Fiber Cable
- ◆ Internal Micro-Lens for Efficient Coupling
- ◆ Inexpensive Plastic Connector Housing
- ◆ Connector-Less Fiber Termination and Connection
- ◆ Interference-Free Transmission from Light-Tight Housing
- ◆ RoHS Compliant

MAXIMUM RATINGS

 $(T_A = 25^{\circ}C)$

Operating and Storage Temperature Range (T_{OP}, T_{STG}) 40° to 85°C
Junction Temperature (T $_J$)85°C
Soldering Temperature (2 mm from case bottom) $(T_S) t \le 5s$ 240°C
Reverse Voltage (V_R)
Power Dissipation (P_{TOT}) $T_A = 25$ °C80 mW
De-rate Above 25°C1.33 mW/°C
Forward Current, DC (I_F) IF-E91A50 mA
Surge Current (I_{FSM}) t ≤ 10 µsec

IF-E91A 1.2 A

CHARACTERISTICS $(T_A=25^{\circ}C)$

Parameter	Symbol	Min.	Тур.	Max.	Unit
Peak Wavelength	$\lambda_{ ext{PEAK}}$		940		nm
Spectral Bandwidth (50% of I _{MAX})	Δλ	-	±20	-	nm
Output Power Coupled into Plastic Fiber (1 mm core diameter). Distance Lens to Fiber<0.1 mm, 1 m SH4001 fiber, I _F =20 mA	$\Phi_{ ext{min}}$	50 -13	70 -11.6	95 -10.2	μW dBm
Switching Times (10% to 90% and 90% to 10%)(R_L =47 Ω , I_F =10 mA)	t _r , t _f	_	1.0	_	μs
Capacitance (f=1 MHz)	C ₀	-	25	_	pF
Forward Voltage	V _f (I _F =20 mA)	_	1.2	1.6	V
	$V_f (I_F=20 \text{ mA})$ $(I_F=50\text{mA})$		1.27	1.6	




FIGURE 1. Normalized power launched versus forward current.




FIGURE 2. Typical spectral output vs. wavelength.




FIGURE 3. Cross-section of fiber optic device.

FIBER TERMINATION INSTRUCTIONS

- 1. Cut off the ends of the optical fiber with a singleedge razor blade or sharp knife. Try to obtain a precise 90-degree angle (square).
- Insert the fiber through the locking nut and into the connector until the core tip seats against the internal micro-lens.
- Screw the connector locking nut down to a snug fit, locking the fiber in place.




FIGURE 4. Case outline.

	MILLIMETERS		INCHES		
DIM	MIN	MAX	MIN	MAX	
Α	23.24	25.27	.915	.995	
В	8.64	9.14	.340	.360	
С	9.91	10.41	.390	.410	
D	1.52	1.63	.060	.064	
Е	4.19	4.70	.165	.185	
F	0.43	0.58	.017	.023	
G	2.54 BSC		.100 BSC		
Н	0.43	0.58	.017	.023	
J	7.62 BSC		.300 BSC		
K	10.80	12.30	.425	.484	
L	1.14	1.65	.045	.065	
М	11.80	13.30	.465	.524	
Ν	2.54 BSC		.100 BSC		
Q	3.05	3.30	.120	.130	
R	10.48	10.99	.413	.433	
S	6.98 BSC		.275 BSC		
U	0.83	1.06	.032	.042	
٧	6.86	7.11	.270	.280	
W	5.08 BSC		.200 BSC		
Χ	10.10	10.68	.397	.427	