

SAW Components

Data Sheet R 770





SAW Components	R 770
Resonator	433,81 / 434,06 MHz

Data Sheet


Features

- 1-port resonator (2 Resonators in 1 housing)
- Provides reliable, fundamental mode, quartz frequency stabilization i.e. in transmitters or local oscillators
- Protection layer: Protec

Terminals

■ Ni, gold plated

Ceramic package QCC8C




Dimensions in mm, approx. weight 0,1 g

Pin configuration

1	Input Reso 1
3	Input Reso 2
7	Output Reso 1
5	Output Reso 2
4,8	Ground (case)
2.6	float

2,6 float



Туре	Ordering code	Marking and Package	Packing		
		according to	according to		
R 770	B39431-R 770-U310	C61157-A7-A56	F61074-V8169-Z000		

Electrostatic Sensitive Device (ESD)

Maximum ratings

Operable temperature range	T_{A}	-45/+120	°C	
Storage temperature range	$T_{\rm stg}$	-45/+120	°C	
DC voltage	$V_{\rm DC}$	12	V	between any terminals
Source power	P_{s}	0	dBm	



SAW Components R 770

433,81 / 434,06 MHz Resonator

Data Sheet

Characteristics Resonator 1

 $T_{A} = 25 \,^{\circ} \text{C}$ $Z_{S} = 50 \,\Omega$ $Z_{L} = 50 \,\Omega$ Reference temperature: Terminating source impedance: Terminating Load impedance:

		min.	typ.	max.	
Center frequency Resonator 11)	f _C	433,76	433,81	433,86	MHz
Frequency offset Resonator 2 to Resonator 1	f _{offset}	200,0	250,0	300,0	KHz
Minimum insertion attenuation	α_{min}	_	1,3	1,7	dB
Unloaded quality factor	Q_{U}	7500	10100	_	
Ageing of $f_{\rm c}$		_	_	± 50	ppm
Equivalent circuit elements					
Motional capacitance	C_1	_	2,12	_	fF
Motional inductance	L_1	_	63,43	_	μΗ
Motional resistance	R_1	_	17	23	Ω
Parallel capacitance ²⁾	C_{01}	_	2,4	_	pF
Temperature coefficient of frequency ³⁾	TC_{f}	_	- 0,03	_	ppm/K ²
Turnover temperature	T_0	5	_	35	°C

¹⁾ Center frequency is defined as the maximum of the real part of the admittance.
2) If used in two port configuration (pin 1-input, pin 7-output) C_0 is reduced by approx. 0,3 pF.
3) Temperature dependence of f_c : $f_c(T_A) = f_c(T_0)(1 + TC_f(T_A - T_0)^2)$



SAW Components R 770

433,81 / 434,06 MHz Resonator

Data Sheet

Characteristics Resonator 2

 $T_{A} = 25 \,^{\circ} \text{C}$ $Z_{S} = 50 \,\Omega$ $Z_{L} = 50 \,\Omega$ Reference temperature: Terminating source impedance: Terminating Load impedance:

		min.	typ.	max.	
Center frequency Resonator 2 ¹⁾	f _C	434,01	434,06	434,11	MHz
Frequency offset Resonator 2 to Resonator 1	f _{offset}	200,0	250,0	300,0	KHz
Minimum insertion attenuation	α_{min}	_	1,3	1,7	dB
Unloaded quality factor	Q_{U}	7500	10100	_	
Ageing of $f_{\rm c}$		_	_	± 50	ppm
Equivalent circuit elements					
Motional capacitance	C_2	_	2,14	_	fF
Motional inductance	L_2	_	62,86	_	μΗ
Motional resistance	R_2	_	17	23	Ω
Parallel capacitance ²⁾	C_{02}	_	2,4	_	pF
Temperature coefficient of frequency ³⁾	TC_{f}	_	- 0,03	_	ppm/K ²
Turnover temperature	T_0	5	_	35	°C

¹⁾ Center frequency is defined as the maximum of the real part of the admittance.
2) If used in two port configuration (pin 3-input, pin 5-output) C_0 is reduced by approx. 0,3 pF.
3) Temperature dependence of f_c : $f_c(T_A) = f_c(T_0)(1 + TC_f(T_A - T_0)^2)$



SAW Components R 770

Resonator 433,81 / 434,06 MHz

Data Sheet

Published by EPCOS AG Surface Acoustic Wave Components Division, SAW CE AE PD P.O. Box 80 17 09, D-81617 München

© EPCOS AG 2004. All Rights Reserved. Reproduction, publication and dissemination of this brochure and the information contained therein without EPCOS' prior express consent is prohibited.

The information contained in this brochure describes the type of component and shall not be considered as guaranteed characteristics. Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.